


Descripción del artículo/Imágenes del producto



Descripción


Material:

Aluminio.

Versión:

Acabado natural.

Planos



Nuestros productos

| Referencia | Perfil | Número de dientes | D | L | L1 |
|-------------|--------|-------------------|-------|-----|-----|
| 22008-05012 | AT5 | 12 | 17,85 | 140 | 125 |
| 22008-05013 | AT5 | 13 | 19,45 | 140 | 125 |
| 22008-05014 | AT5 | 14 | 21,05 | 140 | 132 |
| 22008-05015 | AT5 | 15 | 22,65 | 140 | 132 |
| 22008-05016 | AT5 | 16 | 24,2 | 140 | 140 |
| 22008-05017 | AT5 | 17 | 25,8 | 140 | 140 |
| 22008-05018 | AT5 | 18 | 27,4 | 140 | 140 |
| 22008-05019 | AT5 | 19 | 29 | 140 | 140 |
| 22008-05020 | AT5 | 20 | 30,6 | 160 | 160 |
| 22008-05021 | AT5 | 21 | 32,3 | 160 | 160 |
| 22008-05022 | AT5 | 22 | 33,85 | 160 | 160 |
| 22008-05023 | AT5 | 23 | 35,45 | 160 | 160 |
| 22008-05024 | AT5 | 24 | 37 | 160 | 160 |
| 22008-05025 | AT5 | 25 | 38,6 | 160 | 160 |
| 22008-05026 | AT5 | 26 | 40,2 | 160 | 160 |
| 22008-05027 | AT5 | 27 | 41,8 | 160 | 160 |
| 22008-05028 | AT5 | 28 | 43,35 | 160 | 160 |
| 22008-05030 | AT5 | 30 | 46,55 | 160 | 160 |
| 22008-05032 | AT5 | 32 | 49,7 | 160 | 160 |
| 22008-05034 | AT5 | 34 | 52,85 | 160 | 160 |
| 22008-05036 | AT5 | 36 | 56,05 | 160 | 160 |
| 22008-05038 | AT5 | 38 | 59,25 | 160 | 160 |
| 22008-05040 | AT5 | 40 | 62,45 | 160 | 160 |
| 22008-05042 | AT5 | 42 | 65,6 | 160 | 160 |
| 22008-05044 | AT5 | 44 | 68,8 | 160 | 160 |
| 22008-05046 | AT5 | 46 | 72 | 160 | 160 |
| 22008-05048 | AT5 | 48 | 75,15 | 160 | 160 |
| 22008-05052 | AT5 | 52 | 81,55 | 160 | 160 |
| 22008-05056 | AT5 | 56 | 87,9 | 160 | 160 |
| 22008-05058 | AT5 | 58 | 91,1 | 160 | 160 |

Nuestros productos

| Referencia | Perfil | Número de dientes | D | L | L1 |
|-------------|--------|-------------------|--------|-----|-----|
| 22008-05060 | AT5 | 60 | 94,25 | 160 | 160 |
| 22008-05064 | AT5 | 64 | 100,65 | 160 | 160 |
| 22008-05072 | AT5 | 72 | 113,25 | 160 | 160 |